



450501

Technical properties

Connectivity

Connectors / jacks with 2 integral speaker sockets

Materials

Surface appearance other

Installation, mounting

Installation mode with spreader claws

Connection

Conductor cross-section max. 2.5 mm²

Type of connection with screw terminals

Standards

General standards DIN EN 60130-9

Identification

Application, usage Communication technology

Main design line Communication technology

Instructions

Information text For only 1 loudspeaker socket, use insert for miniature connector order no. 4505 and loudspeaker socket order no. 1800.