



450502

Loudspeaker soc. out. High End, com-tech

Technical properties

Connectivity

Outlet	with straight outlet
Connectors / jacks	banana sockets also suitable for screw connection ; with 2 metal banana plugs, gold-plated design ; with 2 metal banana sockets, gold-plated design

Dimensions

Insertion depth	31 mm
-----------------	-------

Resistance

Connect transition resistance	< 0.15 mΩ
-------------------------------	-----------

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Conductor cross-section	max. 10 mm ²
Clamp transition resistance	< 0.1 mΩ

Scope of delivery

Component	with 2 metal cable lugs, gold-plated design
-----------	---

Safety

REACH conform	Yes
RoHS conform	Yes

Identification

Application, usage	Communication technology
Main design line	Communication technology
With imprint	No

Instructions

Information text	Recommendation: use deep box for larger cross-sections. Jack and plug with red or black identification ring, as well as a plug connection are suitable for protection low voltage.
------------------	--