



4515

### Technical properties

#### Functions

Function Suitable for HDTV

#### Connectivity

Reception / transmission for terrestrial reception ; for digital and analogue transmission

#### Voltage

Voltage disables DC voltage

#### Frequency

Broadband technology 4...2400 MHz

#### Attenuation

Tap loss at 2150 MHz 16 dB

Tap loss at 860 MHz 15 dB

- at 111 ... 862 MHz 15 dB

- at 5 ... 111 MHz 14 dB

- at 950 ... 2400 MHz 16 dB

#### Installation, mounting

System for community, DVB-T and broadband cable systems ; for SAT house distributors

#### Connection

Type of connection with screw terminals

#### Cable

For coaxial cables 75 Ω

#### Equipment

Reverse channel compatible 4...2400 MHz

Decoupling with decoupling device

#### Standards

General standards IEC 169-2 and EN 50083-2 ; EN 60728-4, -11

#### Safety

Shielding value according to EMC protection class A

#### Identification

Application, usage Communication technology

Main design line Communication technology