



4515

Technical properties

Functions

Function Suitable for HDTV

Connectivity

Reception / transmission for terrestrial reception, for digital and analogue transmission

Voltage

Voltage disables DC voltage

Frequency

Broadband technology 4...2400 MHz

Attenuation

Tap loss at 2150 MHz 16 dB

Tap loss at 860 MHz 15 dB

- at 111 ... 862 MHz 15 dB

- at 5 ... 111 MHz 14 dB

- at 950 ... 2400 MHz 16 dB

Materials

Material metal

Installation, mounting

System for community, DVB-T and broadband cable systems, for SAT house distributors

Connection

Type of connection with screw terminals

Cable

For coaxial cables 75 Ω

Equipment

Reverse channel compatible 4...2400 MHz

Decoupling with decoupling device

Standards

General standards IEC 169-2 and EN 50083-2, EN 60728-4, -11

Safety

Shielding value according to EMC protection class A

Identification

Subject to technical modifications

Application, usage

Communication technology

Main design line

Communication technology