



4539

FCC soc. out., 8 /8-pole, cat.3, com-tech, white

Technical properties

Configuration

Category / ports	cat.3
------------------	-------

Compatibility

For registered plugs	RJ 11/12/45
----------------------	-------------

Connectivity

Outlet	with 45° oblique outlet
Plug type	for RJ11, RJ12 and RJ45 plugs

Main electrical features

Rated voltage	125 V DC
Rated current	1 A

Dimensions

Insertion depth	22 mm
-----------------	-------

Frequency

Transmission bandwidth	max. 16 MHz
------------------------	-------------

Resistance

Transition resistance	< 20 mΩ
-----------------------	---------

Materials

Colour independent of design lines	white
Colour	white

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Type of connection	with screw terminals
Cat.3	according to DIN EN 50173
Cat.3 to	according to TIA/IAE-568-B.2

Cable

Conductor Ø	max. 1 mm
-------------	-----------

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

Identification

Application, usage

Communication technology

Main design line

Communication technology