



4562

FCC soc. out., 2 x 8 (4)-pole, cat.3, com-tech, white

Technical properties

Connectivity

Outlet	with 45° oblique outlet
Plug type	for RJ11, RJ12 and RJ45 plugs
Connectors / jacks	parallel contacted sockets

Main electrical features

Rated voltage	125 V DC
Rated current	1 A

Dimensions

Insertion depth	21.5 mm
-----------------	---------

Frequency

Transmission bandwidth	max. 16 MHz
------------------------	-------------

Resistance

Transition resistance	< 20 mΩ
-----------------------	---------

Materials

Colour	white
--------	-------

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Type of connection	with screw terminals
Cat.3	according to DIN EN 50173
Cat.3 to	according to TIA/IAE-568-B.2

Cable

Conductor Ø	max. 1 mm
-------------	-----------

Safety

Protection index IP	IP20
Protection	No

Identification

Application, usage	Communication technology
Main design line	Communication technology