



4562

FCC soc. out., 2 x 8 (4)-pole, cat.3, com-tech, white

Technical properties

Architecture

Design to according to DIN EN 60603-7

Connectivity

Outlet with 45° oblique outlet

Plug type for RJ11, RJ12 and RJ45 plugs

Connectors / jacks parallel contacted sockets

Main electrical features

Rated voltage 125 V DC

Rated current 1 A

Dimensions

Insertion depth 21.5 mm

Frequency

Transmission bandwidth max. 16 MHz

Resistance

Transition resistance < 20 mΩ

Materials

Colour white

Installation, mounting

Installation mode with spreader claws

Connection

Type of connection with screw terminals

Cat.3 according to DIN EN 50173

Cat.3 to according to TIA/IAE-568-B.2

Cable

Conductor Ø max. 1 mm

Safety

Protection No

Identification

Application, usage Communication technology

Main design line Communication technology