



47272045

**SCHUKO soc. out. 45°, R.1/R.3, black glossy**

**Technical properties**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Insertion depth	32 mm
-----------------	-------

**Cover, door**

Cover	Central cover plate
-------	---------------------

**Materials**

Colour of labelling	217,217,217
Colour of design line	black
Colour	black
Colour	deep black
RAL colour	RAL 9005 - Jet black
Material	thermoplastic
Material for printing	PC-PMA black

**Installation, mounting**

Entries	for diagonal insertion
Installation mode	with spreader claws

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

**Settings**

Shading parameter	R1_czarny
Laser parameter	R1_schwarz
<b>Equipment</b>	
Type of configuration	Laserdruck
<b>Safety</b>	
Protection index IP	IP20
Protection	without enhanced contact protection
With enhanced contact protection	No
<b>Identification</b>	
Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1, Berker R.3, Berker R.8
<b>Instructions</b>	
Information text	Specially suited for combining several socket outlets if right angle plugs are used.