



47276084

**Socket outlet 45°, Q.x, alu velvety, lacquered**

**Technical properties**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Insertion depth 32 mm

**Cover, door**

Cover Central cover plate

**Materials**

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance velvety

**Installation, mounting**

Entries for diagonal insertion

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

**Safety**

IK protection code against mechanical impacts 02

REACH conform Yes

RoHS conform Yes

Halogen free No

Protection	without enhanced contact protection
With enhanced contact protection	No
<b>Identification</b>	
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
<b>Instructions</b>	
Information text	Specially suited for combining several socket outlets if right angle plugs are used.