



47287103

**SCHUKO soc. out. 45°, K.5, al., matt, lacq.**

#### Technical properties

##### Architecture

Design according to DIN 49440

##### Configuration

Number of modules 1

##### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

##### Electric current

Rated current 16 A

##### Dimensions

Insertion depth 32 mm

##### Cover, door

Cover Central cover plate

##### Materials

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance matt

##### Installation, mounting

Installation mode with spreader claws

##### Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

##### Use

Differentiation characteristic 1 - Sales with labelling field

##### Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Halogen free	No
Protection	without enhanced contact protection
With enhanced contact protection	No

---

**Identification**

Main design line	Berker K.5
------------------	------------

---

**Instructions**

Information text	Specially suited to combinations of several socket outlets if right angle plugs are used. 1140. Labelling field height designed for 6 mm P-touch strips.
------------------	--