



47287103

**SCHUKO soc. out. 45°, K.5, al., matt, lacq.**

#### Technical properties

##### Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

##### Configuration

Number of modules	1
-------------------	---

##### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

##### Electric current

Rated current	16 A
---------------	------

##### Dimensions

Insertion depth	32 mm
-----------------	-------

##### Cover, door

Cover	Central cover plate
-------	---------------------

##### Materials

Colour of design line	aluminium
Colour	aluminium
Material / workmanship	lacquered
Surface appearance	matt

##### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

##### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1

##### Use

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

##### Safety

IK protection code against mechanical impacts	05
Protection index IP	IP20

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	without enhanced contact protection
With enhanced contact protection	No
<b>Identification</b>	
Main design line	Berker K.5
<b>Instructions</b>	
Information text	Specially suited to combinations of several socket outlets if right angle plugs are used. 1140. Labelling field height designed for 6 mm P-touch strips.