



47357006

SCHUKO soc. out., enhncd contact prot., K.1, ant. matt, lacq.

Technical properties

Architecture

| | |
|-------------|------------------------|
| Design | according to DIN 49440 |
| Fixing mode | flush-mounting |

Configuration

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Rated voltage | 250 V AC |
| Frequency | 50/60 Hz |
| Rated current | 16 A |

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Dimensions

| | |
|---|-------|
| Insertion depth | 32 mm |
| Installation depth, flush-mounted boxes | 31 mm |

Cover, door

| | |
|-------|---------------------|
| Cover | Central cover plate |
|-------|---------------------|

Materials

| | |
|------------------------|------------|
| Colour of design line | anthracite |
| Colour | anthracite |
| Material / workmanship | lacquered |
| Surface appearance | matt |
| Metallic colour | No |

Installation, mounting

| | |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

Connection

| | |
|----------------------|--------------------------|
| Connection terminals | according to IEC 60884-1 |
| Connection terminals | according to VDE 0620-1 |

Use

| | |
|--|--------------------------------|
| Differentiation characteristic 2 - Sales | with enhanced touch protection |
|--|--------------------------------|

Safety

| | |
|---|-----------------------------|
| IK protection code against mechanical impacts | 05 |
| Protection index IP | IP20 |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | No |
| Protection | Enhanced contact protection |
| With enhanced contact protection | Yes |

Identification

| | |
|------------------|------------|
| Main design line | Berker K.1 |
|------------------|------------|