



47397006

SCHUKO soc. out., K.1, ant. matt, lacq.

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line anthracite

Material / workmanship lacquered

Surface appearance matt

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Use

Differentiation characteristic 1 - Sales with labelling field

Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Halogen free	No
Protection	without enhanced contact protection
With enhanced contact protection	No

Identification

Main design line	Berker K.1
------------------	------------

Instructions

Information text	Labelling field height arranged for P-touch strips 6 mm.
------------------	--