



47432045

SCHUKO soc. out., R.1/R.3, black glossy

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

Cover, door

Cover Central cover plate

Materials

Colour of labelling 217,217,217

Colour of design line black

Colour black

Material for printing PC-PMA black

Surface appearance glossy

Metallic colour No

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Settings

Shading parameter R1_czarny

Laser parameter R1_schwarz

Equipment

Type of configuration	Laserdruck
-----------------------	------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

Protection	without enhanced contact protection
------------	-------------------------------------

With enhanced contact protection	No
----------------------------------	----

Identification

Main design line	Berker R.1/R.3/R.8
------------------	--------------------

Secondary design line(s)	Berker R.1 ; Berker R.3 ; Berker R.8
--------------------------	--------------------------------------