



47442045

**SCHUKO soc.out. hinged cover,enhncd contact prot.,var. in 45°step,R.cl**

**Technical properties**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Cover, door**

Hinged covers with self-closing hinged covers

Cover Central cover plate

**Materials**

Colour of labelling 217,217,217

Colour of design line black

Material for printing PC-PMA black

Surface appearance glossy

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

**Settings**

Shading parameter R1\_czarny

Laser parameter R1\_schwarz

**Equipment**

Type of configuration Laserdruck

**Use**

Differentiation characteristic 2 - Sales	enhanced contact protection
Differentiation characteristic 3 - Sales	Mounting orientation variable in 45° steps

### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	Enhanced contact protection
With enhanced contact protection	Yes

### Identification

Main design line	Serie R.classic
------------------	-----------------

### Instructions

Special note text	Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!
Information text	Specially suited for combining several socket outlets if right angle plugs are used.