



47442045

**SCHUKO soc.out. hinged cover,enhncd contact prot.,var. in 45°step,R.cl**

**Technical properties**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Cover, door**

Hinged covers	with self-closing hinged covers
Cover	Central cover plate

**Materials**

Colour of labelling	217,217,217
Colour of design line	black
Colour	black
Material for printing	PC-PMA black

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1

**Settings**

Shading parameter	R1_czarny
Laser parameter	R1_schwarz

**Equipment**

Type of configuration	Laserdruck
-----------------------	------------

**Use**

Differentiation characteristic 2 - Sales	enhanced contact protection
Differentiation characteristic 3 - Sales	Mounting orientation variable in 45° steps
<b>Safety</b>	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes
<b>Identification</b>	
Main design line	Serie R.classic
<b>Instructions</b>	
Special note text	Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!
Information text	Specially suited for combining several socket outlets if right angle plugs are used.