



47442079

**SCHUKO soc.out. hinged cover f.accessible const.,enhncd contact prot.,R.1.3,wh**

**Technical properties**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Insertion depth	32 mm
-----------------	-------

**Cover, door**

Hinged covers	with self-closing hinged covers
Cover	Central cover plate

**Materials**

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

**Use cases**

Barrier-free building	based on DIN 18040
Application	Barrier-free application

**Use**

---

Differentiation characteristic 1 - Sales	with tactile symbol
Differentiation characteristic 2 - Sales	enhanced contact protection

---

**Safety**

---

Protection index IP	IP20
Protection	Enhanced contact protection
With enhanced contact protection	Yes

---

**Identification**

---

Main design line	Berker R.1/R.3
Secondary design line(s)	Berker R.1, Berker R.3, Berker R.8

---