



47446086

SCHUKO soc.out. hinged cover,enhncd contact prot.,var. in 45°step,Q.x,ant.

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Cover, door

Hinged covers with hinged cover that falls back

Cover Central cover plate

Materials

Colour of design line anthracite

Material / workmanship lacquered

Surface appearance velvety

Metallic colour No

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Use

Differentiation characteristic 2 - Sales enhanced contact protection

Differentiation characteristic 3 - Sales Mounting orientation variable in 45° steps

Safety

IK protection code against mechanical impacts 02

REACH conform Yes

RoHS conform	Yes
Halogen free	Yes
Protection	enhanced contact protection VDE 0620-1
With enhanced contact protection	Yes

Identification

Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9

Instructions

Information text	Specially suited for combining several socket outlets if right angle plugs are used.
------------------	--