



47452089

SCHUKO soc. out., mounting orient. var. in 45° steps, R.classic, p. white glossy

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

Cover, door

Cover Central cover plate

Materials

Colour of labelling 105,105,105

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Material for printing ASA polar white

Surface appearance glossy

Metallic colour No

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Equipment

Type of configuration Laserdruck

Use

Differentiation characteristic 3 - Sales

Mounting orientation variable in 45° steps

Safety

REACH conform

Yes

RoHS conform

Yes

Halogen free

Yes

Protection

without enhanced contact protection

With enhanced contact protection

No

Identification

Main design line

Serie R.classic