



474521

SCHUKO soc. out., mounting orient. var. in 45° steps, 1930/glass, black glossy

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line black

Surface appearance glossy

Metallic colour No

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Use

Differentiation characteristic 3 - Sales Mounting orientation variable in 45° steps

Safety

IK protection code against mechanical impacts 02

REACH conform Yes

| | |
|----------------------------------|-------------------------------------|
| RoHS conform | Yes |
| Halogen free | Yes |
| Protection | without enhanced contact protection |
| With enhanced contact protection | No |

Identification

| | |
|--------------------------|---|
| Main design line | Serie 1930/Glas |
| Secondary design line(s) | Serie 1930 ; Serie 1930 Porzellan Made by Rosenthal ; Serie Glass |