



474521

**SCHUKO soc. out., mounting orient. var. in 45° steps, 1930/glass, black glossy**

## Technical properties

### Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

### Configuration

Number of modules	1
-------------------	---

### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

### Electric current

Rated current	16 A
---------------	------

### Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

### Cover, door

Cover	Central cover plate
-------	---------------------

### Materials

Colour of design line	black
Colour	black
Colour	deep black
RAL colour	RAL 9005 - Jet black
Material	duroplastic
Metallic colour	No

### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

### Use

Differentiation characteristic 3 - Sales	Mounting orientation variable in 45° steps
--	--

<b>Safety</b>	
IK protection code against mechanical impacts	02
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	without enhanced contact protection
With enhanced contact protection	No
<b>Identification</b>	
Main design line	Serie 1930/Glas
Secondary design line(s)	Serie 1930, Serie 1930 Porzellan Made by Rosenthal, Serie Glass