



47477104

SCHUKO soc.out. hinged cover,enhncd contact prot.,var. in 45°step,K5,steel

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Installation depth, flush-mounted boxes 35 mm

Cover, door

Hinged covers when opening hinged cover, it can be arrested in end position

Cover Central cover plate

Materials

Colour of design line Stainless steel

Material / workmanship metal, matt finish

Surface appearance matt

Metallic colour Yes

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Use

Differentiation characteristic 2 - Sales enhanced contact protection

Differentiation characteristic 3 - Sales Mounting orientation variable in 45° steps

Safety

IK protection code against mechanical impacts	07
REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	enhanced contact protection VDE 0620-1
With enhanced contact protection	Yes
Identification	
Main design line	Berker K.5