



47477104

**SCHUKO soc.out. hinged cover,enhncd contact prot.,var. in 45°step,K5,steel**

**Technical properties**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Installation depth, flush-mounted boxes	35 mm
---	-------

**Cover, door**

Hinged covers	when opening hinged cover, it can be arrested in end position
Cover	Central cover plate

**Materials**

Colour of design line	Stainless steel
Colour	stainless steel
Colour	stainless steel optics
RAL colour	RAL 9022 - Pearl light grey
Material / workmanship	metal, matt finish
Material	stainless steel
Surface appearance	matt
Metallic colour	Yes

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

**Use**

---

Differentiation characteristic 2 - Sales	enhanced contact protection
Differentiation characteristic 3 - Sales	Mounting orientation variable in 45° steps

---

**Safety**

---

IK protection code against mechanical impacts	07
Protection index IP	IP20
Protection	enhanced contact protection VDE 0620-1
With enhanced contact protection	Yes

---

**Identification**

---

Main design line	Berker K.5
------------------	------------

---