



47496086

SCHUKO soc. out., enhncd contact prot., Q.x, ant. velvety, lacq.

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	anthracite
Colour	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	duroplastic
Surface appearance	velvety
Metallic colour	No

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Use

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

Differentiation characteristic 2 - Sales	enhanced contact protection
--	-----------------------------

Safety

IK protection code against mechanical impacts	02
---	----

Protection index IP	IP20
---------------------	------

Protection	Enhanced contact protection
------------	-----------------------------

With enhanced contact protection	Yes
----------------------------------	-----

Identification

Main design line	Berker Q.1/Q.3/Q.7/Q.9
------------------	------------------------

Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9
--------------------------	--

Instructions

Information text	Labelling field height arranged for P-touch strips 6 mm.
------------------	--