



47501909

**SCHUKO soc. out., S.1/B.3/B.7, p. white, matt, plastic**

#### Technical properties

##### Architecture

Design according to DIN 49440

##### Configuration

Number of modules 1

##### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

##### Electric current

Rated current 16 A

##### Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

##### Cover, door

Cover Central cover plate

##### Materials

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance matt

Metallic colour No

##### Installation, mounting

Installation mode with spreader claws

##### Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

##### Use

Differentiation characteristic 1 - Sales with labelling field

##### Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	without enhanced contact protection
With enhanced contact protection	No

#### Identification

Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7

#### Instructions

Information text	Labelling field height arranged for P-touch strips 6 mm.
------------------	--