



47511909

SCHUKO soc. out. hinged cover, S.1/B.3/B.7, p. white, matt, plastic

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Cover, door

Hinged covers	with hinged cover that falls back
Cover	Central cover plate

Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
Surface appearance	matt

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1

Safety

IK protection code against mechanical impacts	05
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	without enhanced contact protection

With enhanced contact protection		No
Identification		
Main design line		Berker S.1/B.3/B.7
Secondary design line(s)		Berker S.1 ; Berker B.3 ; Berker B.7
Instructions		
Information text		Specially suited for combining several socket outlets if right angle plugs are used.