



47516086

**SCHUKO soc. out. hinged cover, enhncd contact prot., Q.x, ant. velvety lacq.**

#### Technical properties

##### Architecture

Design according to DIN 49440

##### Configuration

Number of modules 1

##### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

##### Electric current

Rated current 16 A

##### Cover, door

Hinged covers with hinged cover that falls back

Cover Central cover plate

##### Materials

Colour of design line anthracite

Material / workmanship lacquered

Surface appearance velvety

Metallic colour No

##### Installation, mounting

Installation mode with spreader claws

##### Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

##### Use

Differentiation characteristic 2 - Sales enhanced contact protection

##### Safety

IK protection code against mechanical impacts 02

REACH conform No

RoHS conform Yes

---

Protection	Enhanced contact protection
------------	-----------------------------

With enhanced contact protection	Yes
----------------------------------	-----

---

**Identification**

Application, usage	Flush-mounted wet-room installation
--------------------	-------------------------------------

Main design line	Berker Q.1/Q.3/Q.7/Q.9
------------------	------------------------

Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
--------------------------	---

---

**Instructions**

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing set (order no. 10107200).
-------------------	--