



47516086

SCHUKO soc. out. hinged cover, enhncd contact prot., Q.x, ant. velvety lacq.

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Cover, door

Hinged covers with hinged cover that falls back

Cover Central cover plate

Materials

Colour of design line anthracite

Material / workmanship lacquered

Surface appearance velvety

Metallic colour No

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Use

Differentiation characteristic 2 - Sales enhanced contact protection

Safety

IK protection code against mechanical impacts 02

REACH conform Yes

RoHS conform Yes

Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes

Identification

Application, usage	Flush-mounted wet-room installation
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9

Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing set (order no. 10107200).
-------------------	------------------------------------------------------------------------------------------------------------------------------------