



47517102

**SCHUKO sock. outl. w. hinged cover a. enhanced cont. protection, K.1, white gl.**

#### Technical properties

##### Architecture

Design	according to DIN 49440
--------	------------------------

##### Configuration

Number of modules	1
-------------------	---

##### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50 Hz
Rated current	16 A

##### Cover, door

Hinged covers	with hinged cover that falls back
Cover	Central cover plate

##### Materials

Colour of design line	white
Surface appearance	glossy
Metallic colour	No

##### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

##### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

##### Use

Differentiation characteristic 2 - Sales	enhanced contact protection
--	-----------------------------

##### Safety

REACH conform	No
RoHS conform	Yes
Halogen free	Yes
Protection	Enhanced contact protection
With enhanced contact protection	Yes

##### Identification

Main design line	Berker K.1
------------------	------------