



47517102

SCHUKO sock. outl. w. hinged cover a. enhanced cont. protection, K.1, white gl.

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50 Hz

Rated current 16 A

Cover, door

Hinged covers with hinged cover that falls back

Cover Central cover plate

Materials

Colour of design line white

Surface appearance glossy

Metallic colour No

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Use

Differentiation characteristic 2 - Sales enhanced contact protection

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Protection Enhanced contact protection

With enhanced contact protection Yes

Identification

Main design line Berker K.1