



47517104

**SCHUKO soc.out. hinged cover, enhncd contact prot., K.5, steel, matt finish**

**Technical properties**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Installation depth, flush-mounted boxes 35 mm

**Cover, door**

Hinged covers with hinged cover that falls back

Cover Central cover plate

**Materials**

Colour of design line Stainless steel

Material / workmanship metal, matt finish

Surface appearance matt

Metallic colour Yes

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

**Use**

Differentiation characteristic 2 - Sales enhanced contact protection

**Safety**

IK protection code against mechanical impacts 07

|                                  |  |
|----------------------------------|--|
| REACH conform                    | No                                     |
| RoHS conform                     | Yes                                    |
| Halogen free                     | No                                     |
| Protection                       | enhanced contact protection VDE 0620-1 |
| With enhanced contact protection | Yes                                    |
| <b>Identification</b>            |  |
| Main design line                 | Berker K.5                             |