



47517106

**SCHUKO soc. out. hinged cover, enhanced contact prot., K.1, ant. matt, lacq.**

**Technical properties**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Cover, door**

Hinged covers with hinged cover that falls back

Cover Central cover plate

**Materials**

Colour of design line anthracite

Material / workmanship lacquered

Surface appearance matt

Metallic colour No

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

**Use**

Differentiation characteristic 2 - Sales enhanced contact protection

**Safety**

IK protection code against mechanical impacts 05

REACH conform No

RoHS conform Yes

Halogen free	Yes
Protection	enhanced contact protection VDE 0620-1
With enhanced contact protection	Yes
<b>Identification</b>	
Main design line	Berker K.1