



47517204

**SCHUKO soc.out. hinged cover, enhanced contact prot., K.5, steel, matt finish**

**Technical properties**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Installation depth, flush-mounted boxes 35 mm

**Cover, door**

Hinged covers with hinged cover that falls back

Cover Central cover plate

**Materials**

Colour of design line Stainless steel

Material / workmanship metal, matt finish

Surface appearance matt

Metallic colour Yes

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

**Use**

Differentiation characteristic 2 - Sales enhanced contact protection

**Safety**

IK protection code against mechanical impacts 07

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	enhanced contact protection VDE 0620-1
With enhanced contact protection	Yes

**Identification**

Application, usage	Flush-mounted wet-room installation
Main design line	Berker K.5

**Instructions**

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing set (order no. 10107200).
-------------------	--