



47517209

**SCHUKO soc. out. hinged cover, enhncd contact prot., K.1, p. white glossy**

**Technical properties**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Cover, door**

Hinged covers with hinged cover that falls back

Cover Central cover plate

**Materials**

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance glossy

Metallic colour No

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

**Use**

Differentiation characteristic 2 - Sales enhanced contact protection

**Safety**

IK protection code against mechanical impacts 05

REACH conform Yes

|                                  |  |
|----------------------------------|--|
| RoHS conform                     | Yes  |
| Halogen free                     | Yes  |
| Protection                       | enhanced contact protection VDE 0620-1   |
| With enhanced contact protection | Yes  |
| <b>Identification</b>            |  |
| Application, usage               | Flush-mounted wet-room installation  |
| Main design line                 | Berker K.1   |
| <b>Instructions</b>              |  |
| Special note text                | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing set (order no. 10107200). |