



47526086

SCHUKO soc. out. hinged cover, enhncd contact prot., Q.x, ant. velvety lacq.

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Cover, door

Hinged covers with self-closing hinged covers

Cover Central cover plate

Materials

Colour of design line anthracite

Material / workmanship lacquered

Surface appearance velvety

Metallic colour No

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Use

Differentiation characteristic 1 - Sales Labelling field

Differentiation characteristic 2 - Sales enhanced contact protection

Safety

| | |
|---|-----------------------------|
| IK protection code against mechanical impacts | 02 |
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | No |
| Protection | Enhanced contact protection |
| With enhanced contact protection | Yes |

Identification

| | |
|--------------------------|---|
| Application, usage | Flush-mounted wet-room installation |
| Main design line | Berker Q.1/Q.3/Q.7/Q.9 |
| Secondary design line(s) | Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9 |

Instructions

| | |
|-------------------|--|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing set (order no. 10107200). |
| Information text | Labelling field height arranged for P-touch strips 6 mm. |