



47526086

**SCHUKO soc. out. hinged cover, enhanced contact protection, Q.x, ant. velvety lacq.**

#### Technical properties

##### Architecture

Design	according to DIN 49440
--------	------------------------

##### Configuration

Number of modules	1
-------------------	---

##### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

##### Electric current

Rated current	16 A
---------------	------

##### Dimensions

Insertion depth	32 mm
-----------------	-------

##### Cover, door

Hinged covers	with self-closing hinged covers
Cover	Central cover plate

##### Materials

Colour of design line	anthracite
Material / workmanship	lacquered
Surface appearance	velvety
Metallic colour	No

##### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

##### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

##### Use

Differentiation characteristic 1 - Sales	Labelling field
Differentiation characteristic 2 - Sales	enhanced contact protection

##### Safety

IK protection code against mechanical impacts	02
REACH conform	No
RoHS conform	Yes
Protection	Enhanced contact protection
With enhanced contact protection	Yes

#### Identification

Application, usage	Flush-mounted wet-room installation
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9

#### Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing set (order no. 10107200).
Information text	Labelling field height arranged for P-touch strips 6 mm.