



47537004

Double SCHUKO soc. out. cover plate, K.5, stainless steel matt, lacq.

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	2
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Assembling height	22 mm
-------------------	-------

Cover, door

Cover	Full cover plate
-------	------------------

Materials

Colour of design line	stainless steel
Colour	stainless steel
Colour	stainless steel optics
RAL colour	RAL 9022 - Pearl light grey
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	matt

Installation, mounting

For installation in 1gang wall boxes	according to DIN 49073-1
Installation mode	with spreader claws

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Safety

Protection index IP	IP20
Protection	without enhanced contact protection

Identification

Main design line	Berker K.5
------------------	------------