



47552045

SCHUKO soc.out.,enhncd contact prot.,mounting orient. var. in 45°step,R.cl,bl.

#### Technical properties

##### Architecture

Design according to DIN 49440

##### Configuration

Number of modules 1

##### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

##### Electric current

Rated current 16 A

##### Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

##### Cover, door

Cover Central cover plate

##### Materials

Colour of labelling 217,217,217

Colour of design line black

Material for printing PC-PMA black

Surface appearance glossy

Metallic colour No

##### Installation, mounting

Installation mode with spreader claws

##### Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

##### Equipment

Type of configuration Laserdruck

##### Use

---

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales Mounting orientation variable in 45° steps

---

**Safety**

---

REACH conform Yes

---

RoHS conform Yes

---

Halogen free Yes

---

Protection Enhanced contact protection

---

With enhanced contact protection Yes

---

**Identification**

---

Main design line Serie R.classic