



503203

Push-button NC contact and NO contact with isolated input terminals

Technical properties

Architecture

Type of control unit rocker

Functions

Switching angle 3.5 °

Configuration

Switch mode 1 NO, 1 NC, separate input terminals

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 41.6 mm

Insertion depth 30.9 mm

Height 71 mm

Width 71 mm

Materials

Material Plastic/metal

Installation, mounting

Installation mode with spreader claws

Equipment

Quantity of NC contacts 1

Quantity of NO contacts 1

Lighting for lighting and monitoring circuit

Use cases

Application Barrier-free application, HVAC-control, Light control

Safety

Protection index IP IP20

Identification

Main design line

Light control

Instructions

Information text

spreader claws, insulated to the supporting ring, self-
resetting