



503404

Group push-button, 4NO contacts, comm. input terminal, neut. pos., light control

Technical properties

Architecture

Type of control unit double rocker

Configuration

Switch mode with neutral position

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 41.6 mm

Contact spacing > 3 mm

Height 71 mm

Width 71 mm

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with screw terminals

Type of connection Screw connection

Equipment

Lighting for illumination

Use cases

Application Blind control ; Light control

Use

Differentiation characteristic 3 - Sales with neutral-position

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No
Identification	
Application, usage	Light control
Main design line	Light control
Instructions	
Information text	spreader claws, insulated to the supporting ring, self-resetting