



503520

## Blind push-button 1pole, blind control

### Technical properties

#### Architecture

Type of control unit	double rocker
----------------------	---------------

#### Functions

Switching angle	3.5 °
-----------------	-------

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V
Frequency	50/60 Hz

#### Electric current

Momentary-contact current	10 A
---------------------------	------

#### Dimensions

Depth	42 mm
Insertion depth	31.2 mm
Height	70.8 mm
Width	70.8 mm

#### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

#### Use cases

Application	Blind control
-------------	---------------

#### Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

#### Identification

Application, usage	Blind control
Main design line	Blind control