



503808

Series push-button 2 change-over contacts with isolated input terminals

Technical properties

Architecture

Type of control unit double rocker

Configuration

Switch mode double change-over contact, usable as NC or NO with separate input terminals

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 41.6 mm

Height 71 mm

Width 71 mm

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with screw terminals

Type of connection Screw connection

Scope of delivery

With lamp No

Equipment

Quantity of NC contacts 1

Quantity of NO contacts 1

Lighting for illumination

Use cases

Application Light control

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Identification

Application, usage	Light control
Main design line	Light control

Instructions

Information text	spreader claws, insulated to the supporting ring, self-resetting
------------------	------------------------------------------------------------------
