



503808

## Series push-button 2 change-over contacts with isolated input terminals

### Technical properties

#### Architecture

Type of control unit double rocker

#### Configuration

Switch mode double change-over contact, usable as NC or NO with separate input terminals

Antibacterial treatment No

#### Compatibility

IFTTT support available No

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

#### Electric current

Momentary-contact current 10 A

#### Dimensions

Depth 41.6 mm

Height 71 mm

Width 71 mm

#### Materials

Material Plastic/metal

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with screw terminals

Type of connection Screw connection

#### Scope of delivery

With lamp No

#### Equipment

Quantity of NC contacts 1

Quantity of NO contacts 1

Lighting for illumination

**Use cases**

---

Application

Light control

**Safety**

---

Protection index IP

IP20

**Identification**

---

Application, usage

Light control

Main design line

Light control

**Instructions**

---

Information text

spreader claws, insulated to the supporting ring, self-resetting