



503808

Series push-button 2 change-over contacts with isolated input terminals

Technical properties

Architecture

Type of control unit	double rocker
----------------------	---------------

Configuration

Switch mode	double change-over contact, usable as NC or NO with separate input terminals
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

Electric current

Momentary-contact current	10 A
---------------------------	------

Dimensions

Depth	41.6 mm
Height	71 mm
Width	71 mm

Materials

Material	Plastic/metal
----------	---------------

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60669-1
Connection terminals	according to VDE 0632-1
Type of connection	with screw terminals
Type of connection	Screw connection

Scope of delivery

With lamp	No
-----------	----

Equipment

Quantity of NC contacts	1
Quantity of NO contacts	1
Lighting	for illumination

Use cases	
Application	Light control
Safety	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Identification	
Application, usage	Light control
Main design line	Light control
Instructions	
Information text	spreader claws, insulated to the supporting ring, self-resetting