



633023

Rocker switch 3 x 1-pole Off, Module inserts

Technical properties

Architecture

Type of control unit single rocker

Configuration

Switch mode 3 x 1- pole Off

Antibacterial treatment No

Compatibility

IFTTT support available No

Controls and indicators

Push-buttons No

Main electrical features

Nominal voltage 400 V

Frequency 50/60 Hz

Electric current

Switching current 16 AX (200 W Self Ballasted Lamp (SBL))

Dimensions

Depth 42 mm

Height 71 mm

Width 71 mm

Connection

Type of connection with screw terminals

Type of connection Screw connection

Equipment

Lighting without lighting (cannot be illuminated)

Heating switch No

Use cases

Application Light control

Safety

Impact strength IK07

Identification

Appliance switch type No