



633023

Rocker switch 3 x 1-pole Off, Module inserts

Technical properties

Architecture

Type of control unit	single rocker
Fixing mode	flush-mounting

Configuration

Switch mode	3 x 1- pole Off
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Controls and indicators

Push-buttons	No
--------------	----

Main electrical features

Nominal voltage	400 V
Frequency	50/60 Hz

Electric current

Switching current	16 AX (200 W Self Ballasted Lamp (SBL))
-------------------	---

Dimensions

Depth	42 mm
Height	71 mm
Width	71 mm

Materials

Material	Plastic/metal
----------	---------------

Connection

Type of connection	with screw terminals
Type of connection	Screw connection

Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

Use cases

Application	Light control
-------------	---------------

Safety

Protection index IP	IP20
---------------------	------

Identification

Appliance switch type

No