



75141326



IP20



Technical properties

Functions

With room temperature controller	No
Function	for switch, push-button, dimmer and shutter functions
Light scenes	retrieval, adjustment and storage of 8 light scenes

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
Number of buttons	1
Operation	one push-button operation for switching, pushing, shutters and dimming

Dimensions

Labelling field length (W x H)	56.4 mm
Height	71 mm
Width	71 mm

Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

Screen

With display	No
--------------	----

Materials

Colour of labelling	217,217,217
Colour of design line	anthracite
Material for printing	Paper
Surface appearance	velvety
Type of surface treatment	untreated
Material family	Plastic

LED control

LED	with white operation LED and 2 amber status LEDs
-----	--

Settings

Supported configuration modes	system
Parameterisation	single and two push-button operation parameterisable

Scope of delivery	
Bus connection included	Yes
Equipment	
Number of actuation points	2
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 1gang
Controller extension unit	usable as thermostat extension unit
Use	
Differentiation characteristic 1 - Sales	with labelling field
Differentiation characteristic 3 - Sales	with integral bus coupling unit
Safety	
Protection	with dismantling protection
Use conditions	
Operating temperature	-5...45 °C
Identification	
Application, usage	KNX - operating systems
Product family	product family: push-button
Secondary design line(s)	KNX ; Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
Instructions	
Information text	Labelling field sheet, order no. 9498 29 01, available separately.