



75141326

IP20



## Technical properties

### Architecture

Fixing mode flush-mounting

### Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Light scenes retrieval, adjustment and storage of 8 light scenes

### Compatibility

Extension unit extension unit for light scene push-button

### Controls and indicators

With LED indication Yes

Number of buttons 1

Operation one push-button operation for switching, pushing, shutters and dimming

### Dimensions

Labelling field length (W x H) 56.4 mm

Height 71 mm

Width 71 mm

### Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

### Screen

With display No

### Materials

Colour of labelling 217,217,217

Colour of design line anthracite

Colour anthracite

RAL colour RAL 7021 - Black grey

Material Plastic/metal

Material for printing Paper

Surface appearance velvety

Type of surface treatment untreated

Material family Plastic

### LED control

LED with white operation LED and 2 amber status LEDs

### Settings

Supported configuration modes system

Parameterisation single and two push-button operation parameterisable

### Scope of delivery

Bus connection included Yes

### Equipment

Number of actuation points 2

With anti-theft/dismantling protection Yes

Type of configuration Beschriftungsfeld(er) - Folie

Product type: product type: push-button 1gang

Controller extension unit usable as thermostat extension unit

### Use

Differentiation characteristic 1 - Sales with labelling field

Differentiation characteristic 3 - Sales with integral bus coupling unit

### Safety

Protection index IP IP20

Protection with dismantling protection

### Use conditions

Operating temperature -5...45 °C

### Identification

Application, usage KNX - operating systems

Product family product family: push-button

Secondary design line(s) KNX, Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

### Instructions

Information text Labelling field sheet, order no. 9498 29 01, available separately.