



75142226



IP20



## Technical properties

### Architecture

Fixing mode flush-mounting

### Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

### Compatibility

Extension unit extension unit for light scene push-button

### Controls and indicators

With LED indication Yes

Number of buttons 2

### Dimensions

Labelling field length (W x H) 56.4 x 26.8 mm

Height 71 mm

Width 71 mm

### Measurement

Value transmitter dimming / position value transmitter 1 byte

### Screen

With display No

### Materials

Colour of labelling 217,217,217

Colour of design line anthracite

Colour anthracite

RAL colour RAL 7021 - Black grey

Material thermoplastic

Material for printing Paper

Surface appearance velvety

Type of surface treatment Painted

Material family Plastic

### LED control

LED with white operation LED and 4 amber status LEDs

### Scope of delivery

Bus connection included Yes

**Equipment**

Number of actuation points	4
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 2gang

**Use**

Differentiation characteristic 1 - Sales	with labelling fields
Differentiation characteristic 3 - Sales	with integral bus coupling unit

**Safety**

Protection index IP	IP20
Protection	with dismantling protection

**Use conditions**

Operating temperature	-5...45 °C
-----------------------	------------

**Identification**

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker Q.1/Q.3
Secondary design line(s)	Berker Q.3, KNX, Berker Q.1

**Instructions**

Information text	Labelling field sheet, order no. 9498 30 02, available separately.
------------------	--