


75143226

IP20



Technical properties

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 3

Dimensions

Labelling field length (W x H) 56.4 x 17 mm

Height 71 mm

Width 71 mm

Measurement

Value transmitter dimming / position value transmitter 1 byte

Screen

With display No

Materials

Colour of labelling 217,217,217

Colour of design line anthracite

Colour anthracite

RAL colour RAL 7021 - Black grey

Material thermoplastic

Material for printing Paper

Surface appearance velvety

Type of surface treatment Painted

Material family Plastic

LED control

LED with white operation LED and 6 amber status LEDs

Scope of delivery

Bus connection included Yes

Equipment

Number of actuation points	6
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 3gang

Use

Differentiation characteristic 1 - Sales	with labelling fields
Differentiation characteristic 3 - Sales	with integral bus coupling unit

Safety

Protection index IP	IP20
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker Q.1/Q.3
Secondary design line(s)	KNX, Berker Q.3, Berker Q.1

Instructions

Information text	Labelling field sheet, order no. 9498 31 03, available separately.
------------------	--